### **Optical Chopper – Ultra Miniature**

### Model 360C





#### **Features**


- → 10Hz 14kHz standard chopping frequency range
- → 30mm diameter chopping discs
- → Photochemically etched, non-magnetic discs
- → Ultra compact chopper head
- → Small size drive board
- → Low cost, for OEM applications
- Scitec Instruments Model 360 optical chopper system consists of a chopper head, drive board, photochemically etched discs and an interconnecting cable. This optical chopper uses 30mm diameter discs.
- The drive board and chopping head have been designed to be as compact as possible to allow positioning in areas where space is critical. As the system is designed for OEM use, each component is available separately.



# Specifications 360H Chopping Head

- → **Motor:** 5 pole DC motor, sleeve bearings with 1000 hours lifetime, 0-15000 rpm reversible.
- Reference pick-up: IR led and phototransistor pair with Schmitt trigger.
- → **Dimensions:** 43(H) x 30(L) x 14(W) mm without blade.
- → **Dimensions:** 50(H) x 30(L) x 30(W) mm with blade.
- → **Mounting:** Two 3 mm holes near base.





Model\_360C\_issue1.2 [page 1 of 2]

## Optical Chopper – Ultra Miniature

#### Model 360C





#### 360C OEM Drive Board

- → Input Voltage: 7V to 15V DC or 9V to 18V AC
- Frequency Control: On board trim, external potentiometer or external voltage
- Frequency Stability: Short term see phase jitter. Long term - ±1% of max frequency within 10 to 100% of maximum frequency.
- → Reference output: 5 V HCT TTL signal via jack socket
- → Power Requirement: 60mA no load, 80mA max
- → Dimensions: 43 x 73 mm
- → Weight: 25 g




- → Disc types: 2, 4, 10 and 40 slot (20 and 80 slot discs are also available).
- → Material: Half hard brass, 0.25mm thick.
- → Diameter: 30 mm.
- → Surface Finish: Chemically blacked.
- → Mark-Space Ratio: 1:1.





#### Frequency Range

Blade	Frequency (Hz)	Aperture (mm)				Phase Jitter Max
		r	а	b	d	
350D2 (2 slots)	10 - 325	9.0	23.6	9.4	9.0	TBA
350D4 (4 slots)	20 - 650	9.0	11.8	4.7	8.3	TBA
350D10 (10 slots)	50 - 1500	8.0	4.4	1.9	3.7	TBA
350D20 (20 slots)	100 - 3000	8.0	2.2	0.94	2.0	TBA
350D40 (40 slots)	200 - 6000	8.0	1.1	0.47	1.0	TBA
350D80 (80 slots)	400 - 12000	5.0	0.55	0.35	0.5	TBA



#### **Ordering Information**

**Model 360C Optical Chopper:** The 360 system is available as separate components as most customers require only some of the following parts:

- Model 360C OEM Drive board, chopping head, interconnecting lead and 2 discs (please specify when ordering).
- → 360C OEM Drive board
- → 360H Chopping head
- → 360I Interconnecting lead, 1 m in length
- → 350D2 Two slot 30mm disc
- → 350D4 Four slot 30mm disc
- → 350D10 Ten slot 30mm disc
- → 350D20 Twenty slot 30mm disc
- → 350D40 Forty slot 30mm disc
- → 350D80 Eighty slot 30mm disc
- → 350D Set of 4 discs (350D2, 350D4, 350D10 & 350D40)

Please note, a complete system also requires a wall mounted power supply which is available from many sources.

#### **Enquiries**

- → Scitec Instruments Ltd Unit 6 Sandown Centre White Horse Business Park Trowbridge Wiltshire BA14 0XD UK
- → t. +44 [0]1225 751 542
- → www.scitec.uk.com
- → e. sales@scitec.uk.com

Model\_360C\_issue1.2 [page 2 of 2]